

YDSR26RL

by Burndy
Catalog ID: YDSR26RL

Prop 65 Notice

Extra long replacement splice designed to facilitate the permanent replacement of an existing line splice. Eliminates need for two splices and extra conductor.



Product Details

General

Connector Type	Splice
Die Index	659
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810503232

Dimensions

Dimension - B Length inch	6.70 in
Dimension - L Length Overall mm	902 mm
Dimension - Length Overall inch	35.50 in
Dimension - Outside Diameter inch	.83 in

Conductor Related

Conductor - AAAC 5005 Size	2/0 AWG
Conductor - AAAC 6201 Size	2/0 AWG
Conductor - ACSR Cmpt Size	2/0 AWG
Conductor - ACSR Cmpt Size Range	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)