

# YDSR2RL

by Burndy  
Catalog ID: YDSR2RL

Prop 65 Notice

Extra long replacement splice designed to facilitate the permanent replacement of an existing line splice. Eliminates need for two splices and extra conductor.



## Product Details

### General

Connector Type	Splice
Die Index	BG;687;243
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810503188

### Dimensions

Dimension - B Length inch	5.04 in
Dimension - L Length Overall mm	711 mm
Dimension - Length Overall inch	28.00 in
Dimension - Outside Diameter inch	.66 in

### Conductor Related

Conductor - AAAC 5005 Size	2 AWG
Conductor - AAAC 6201 Size	2 AWG
Conductor - ACSR Str Size	2 AWG
Conductor - AL Str Size	2 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)