



YE26P31X109

by Burndy
Catalog ID: YE26P31X109

Prop 65 Notice

Cu Adaptor Plugs, N125 2/0 AWG STR Cu, 2.29 IN L, Compression, Black, 13 Index, 1.00 IN Strip Length

Product Details

General

Color Code	Black
Connector Type	Pin Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810006153
UPC 12 Digit	7818100061533

Dimensions

Dimension - A Outside Diameter inch	0.31 in
Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - B Outside Diameter inch	0.56 in
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.29 in
Dimension - Outside Diameter inch	0.56 in
Dimension - P inch	1.09 in
Dimension - Strip Length inch	1.00 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size Range	2/0 AWG
-----------------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)