

YE28R60

by Burndy
Catalog ID: YE28R60

Prop 65 Notice

Terminal Plug for AL and ACSR, 4/0 AL,4/0 ACSR, 9.5 in Length, Tin Plated, Pink, 840 or 249 or 11A Index.

Features: Aluminum HYPLUG With Tin-Plated Copper Plug For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor, Plug May Be Bent To Desired Angle For Easier Insertion, Three Die Sets Accommodate 4 AWG Stranded - 500 KCMIL, Terminals Are Pre-Filled With PENE -TROX A-13 Joint Compound And Sealed With Color Coded End Caps, Die Index: 249 Or 840 Element A, Color Code: Pink, Plug/pin Diameter: 3/8 IN, Plug/pin Length: 6 IN, Tools, Die Set Catalog Number, And (number Of Crimps): MD7, MD6 Tool, W249 Or W-K840 Die, Y750, Y35 Tool, U249, U-K840T Die, Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1, Y48BH Tool, C249 Die, Y60BH Tool, L249 Die



Product Details

General

Application	For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor
Color Code	Pink
Die Index	249;840;11A
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154304

Dimensions

Dimension - L Length Overall mm	241 mm
Dimension - Length Overall inch	9.50 in
Dimension - Outside Diameter inch	0.91 in
Dimension - P inch	6 in

Conductor Related

Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)