

YE29P41X82

by Burndy
Catalog ID: YE29P41X82

Prop 65 Notice

Cu Adaptor Plugs, 250 KCMIL (Code), 3.15 IN L, Compression, Yellow, 16 Index, 2-1/2 IN Strip Length



Product Details

General

Color Code	Yellow
Connector Type	Pin Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810038994
UPC 12 Digit	7818100389944

Dimensions

Dimension - A Outside Diameter inch	0.41 in
Dimension - B Length fraction	2 in
Dimension - B Length inch	1.99 in
Dimension - B Outside Diameter inch	0.75 in
Dimension - Inside Diameter inch	0.6 in
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.15 in
Dimension - Outside Diameter inch	0.75 in
Dimension - P inch	0.82 in
Dimension - Strip Length inch	2-1/2 in
Equivalent Cross Pin Size	0.41 in. - 3/0 AWG
Equivalent Pin Size	3/0 AWG

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size Range	250 kcmil
Conductor - Copper Flex H Size Range	250 kcmil
Conductor - Copper Flex I Size Range	250 kcmil
Conductor - Copper Flex K Size Range	250 kcmil
Conductor - Copper Flex M Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)