

YE30P46X92FX

by Burndy
Catalog ID: YE30P46X92FX

Prop 65 Notice

Copper Adaptor Plugs, 250 kcmil Flex CLASS G 259 CLASS H 427, 16
Index, Cable Strip Length: 2-3/8 IN



Product Details

General

Color Code	Yellow
Connector Type	Pin Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810037867
UPC 12 Digit	7818100378677

Dimensions

Dimension - A Outside Diameter inch	0.46 in
Dimension - B Length fraction	2-3/8 in
Dimension - B Length inch	2.37 in
Dimension - B Outside Diameter inch	0.81 in
Dimension - Inside Diameter inch	0.65 in
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.67 in
Dimension - Outside Diameter inch	0.81 in
Dimension - P inch	0.92 in
Dimension - Strip Length inch	3.34 in
Equivalent Cross Pin Size	0.46 in. - 4/0 AWG
Equivalent Pin Size	4/0 AWG

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	250 kcmil
Conductor - Copper Flex G Size Range	259
Conductor - Copper Flex H Size	250 kcmil
Conductor - Copper Flex H Size Range	427
Conductor - Copper Flex I Size Range	250
Conductor - Copper Flex K Size Range	250
Conductor - Copper Flex M Size Range	250
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)