

YE30P55X110

by Burndy
Catalog ID: YE30P55X110

Prop 65 Notice

Cu Adaptor Plugs, 300 KCMIL (Code), 3.85 IN L, Compression, White, 17 Index, 2-5/8 IN Strip Length



Product Details

General

Color Code	White
Connector Type	Pin Terminal
Die Index	17
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810037812
UPC 12 Digit	7818100378122

Dimensions

Dimension - A Outside Diameter inch	0.55 in
Dimension - B Length fraction	2-3/8 in
Dimension - B Length inch	2.37 in
Dimension - B Outside Diameter inch	0.81 in
Dimension - Inside Diameter inch	0.65 in
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.85 in
Dimension - Outside Diameter inch	0.81 in
Dimension - P inch	1.10 in
Dimension - Strip Length inch	2-5/8 in
Equivalent Cross Pin Size	0.55 in. - 300 kcmil
Equivalent Pin Size	300 kcmil

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size Range	300 kcmil
Conductor - Copper Flex H Size Range	300 kcmil
Conductor - Copper Flex I Size Range	300 kcmil
Conductor - Copper Flex K Size Range	300 kcmil
Conductor - Copper Flex M Size Range	300 kcmil
Conductor - Copper Str Size	300 kcmil
Conductor - Copper Str Size Range	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)