

# YE32P46X92FX

by Burndy  
Catalog ID: YE32P46X92FX

Prop 65 Notice

Cu Compression Adaptor Plugs, 313.1 kcmil (775/#24)DLO (300 kcmil Nom.), 4/0 Pin Size



## Product Details

### General

Color Code	Red
Connector Type	Pin Terminal
Die Index	18
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810037980
UPC 12 Digit	7818100379800

### Dimensions

Dimension - A Outside Diameter inch	0.46 in
Dimension - B Length fraction	2-9/16 in
Dimension - B Length inch	2.53 in
Dimension - B Outside Diameter inch	0.95 in
Dimension - Inside Diameter inch	0.76 in
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.90 in
Dimension - Outside Diameter inch	0.95 in
Dimension - P inch	0.92 in
Dimension - Strip Length inch	2.63 in
Equivalent Cross Pin Size	0.46 in. - 4/0 AWG
Equivalent Pin Size	4/0 AWG

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	313 DLO
Conductor - Copper DLO Size Range	313.1 (775/#24) DLO
Conductor - Copper Flex G Size	300 kcmil
Conductor - Copper Flex H Size	300 kcmil
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex K Size	300 kcmil
Conductor - Copper Flex M Size	300 kcmil
Conductor - Copper Str Size	300 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)