

YE32P55X110FX

by Burndy
Catalog ID: YE32P55X110FX

Prop 65 Notice

Cu Adaptor Plugs, 313.1 kcmil (775/#24) DLO, 300 kcmil NOM Flex, 600V, Compression



Product Details

General

Color Code	Red
Connector Type	Pin Terminal
Die Index	18
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810037737
UPC 12 Digit	7818100377377

Dimensions

Dimension - A Outside Diameter inch	0.55 in
Dimension - B Length fraction	2-9/16 in
Dimension - B Length inch	2.53 in
Dimension - B Outside Diameter inch	0.95 in
Dimension - Inside Diameter inch	0.76 in
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.08 in
Dimension - Outside Diameter inch	0.95 in
Dimension - P inch	1.10 in
Dimension - Strip Length inch	2.63 in
Equivalent Cross Pin Size	0.55 in. - 300 kcmil
Equivalent Pin Size	300 kcmil

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	313 DLO
Conductor - Copper DLO Size Range	313.1 (775/#24) DLO
Conductor - Copper Flex G Size	300 kcmil
Conductor - Copper Flex H Size	300 kcmil
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex K Size	300 kcmil
Conductor - Copper Flex M Size	300 kcmil
Conductor - Copper Str Size	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)