

# YE34P55X110FX

by Burndy  
Catalog ID: YE34P55X110FX

Prop 65 Notice

Cu Compression Adaptor Plugs, 373.7 kcmil(925/#24)DLO (353 kcmil Nom.), 4.28" L



## Product Details

### General

Color Code	Blue
Connector Type	Pin Terminal
Die Index	19
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810038260
UPC 12 Digit	7818100382600

### Dimensions

Dimension - A Outside Diameter inch	0.55 in
Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.68 in
Dimension - B Outside Diameter inch	1.06 in
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	109 mm
Dimension - Length Overall inch	4.28 in
Dimension - Outside Diameter inch	1.06 in
Dimension - P inch	1.10 in
Dimension - Strip Length inch	2.75 in
Equivalent Cross Pin Size	0.55 in. - 300 kcmil
Equivalent Pin Size	300 kcmil

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	373 DLO
Conductor - Copper DLO Size Range	373.7 (925/#24) DLO
Conductor - Copper Flex G Size	350 kcmil
Conductor - Copper Flex H Size	350 kcmil
Conductor - Copper Flex I Size	350 kcmil
Conductor - Copper Flex K Size	350 kcmil
Conductor - Copper Flex M Size	350 kcmil
Conductor - Copper Str Size	350 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)