



YE36P62X156

by Burndy
Catalog ID: YE36P62X156

Prop 65 Notice

Cu Adaptor Plugs, 600 KCMIL Cu, 3.78 IN L, Compression, Green, 22 Index,
1.75 IN Strip Length

Product Details

General

Color Code	Green
Connector Type	Pin Terminal
Die Index	22
Feature - Barrel Style	Chamfered
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810006214
UPC 12 Digit	7818100062144

Dimensions

Dimension - A Outside Diameter inch	0.62 in
Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - B Outside Diameter inch	1.19 in
Dimension - L Length Overall mm	96 mm
Dimension - Length Overall inch	3.78 in
Dimension - Outside Diameter inch	1.19 in
Dimension - P inch	1.56 in
Dimension - Strip Length inch	1.75 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)