

YE36P63X126

by Burndy
Catalog ID: YE36P63X126

Prop 65 Notice

Cu Adaptor Plugs, 600 KCMIL (Code), 4.95 IN L, Compression, Green, 22 Index, 3-7/16 IN Strip Length



Product Details

General

Color Code	Green
Connector Type	Pin Terminal
Die Index	22
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810039007
UPC 12 Digit	7818100390077

Dimensions

Dimension - A Outside Diameter inch	0.63 in
Dimension - B Length fraction	3-1/8 in
Dimension - B Length inch	3.14 in
Dimension - B Outside Diameter inch	1.19 in
Dimension - Inside Diameter inch	0.92 in
Dimension - L Length Overall mm	126 mm
Dimension - Length Overall inch	4.95 in
Dimension - Outside Diameter inch	1.19 in
Dimension - P inch	1.26 in
Dimension - Strip Length inch	3.44 in
Equivalent Cross Pin Size	0.63 in. - 400 kcmil
Equivalent Pin Size	400 kcmil

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size Range	600 kcmil
Conductor - Copper Flex H Size Range	600 kcmil
Conductor - Copper Flex I Size Range	600 kcmil
Conductor - Copper Flex K Size Range	600 kcmil
Conductor - Copper Flex M Size Range	600 kcmil
Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)