

YE36P67X134FX

by Burndy
Catalog ID: YE36P67X134FX

Prop 65 Notice

Copper Adaptor Plug; 444.4 kcmil; 5.04 IN L; 20 Index



Product Details

General

Color Code	Brown
Connector Type	Pin Terminal
Die Index	20
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810038147
UPC 12 Digit	7818100381477

Dimensions

Dimension - A Outside Diameter inch	0.67 in
Dimension - B Length fraction	3-1/8 in
Dimension - B Length inch	3.14 in
Dimension - B Outside Diameter inch	1.19 in
Dimension - Inside Diameter inch	0.92 in
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.04 in
Dimension - Outside Diameter inch	1.19 in
Dimension - P inch	1.34 in
Dimension - Strip Length inch	3.75 in
Equivalent Cross Pin Size	0.67 in. - 450 kcmil
Equivalent Pin Size	450 kcmil

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	444 DLO
Conductor - Copper DLO Size Range	444.4 (1100/#24) DLO
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Str Size	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)