

# YE38P59X118FX

by Burndy  
Catalog ID: YE38P59X118FX

Prop 65 Notice

Cu Adaptor Plugs, 535.3 kcmil (1325/#24) DLO, 500 kcmil NOM Flex, 600V, Compression



## Product Details

### General

Color Code	Pink
Connector Type	Pin Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810038222
UPC 12 Digit	7818100382222

### Dimensions

Dimension - A Outside Diameter inch	0.59 in
Dimension - B Length fraction	3-5/16 in
Dimension - B Length inch	3.29 in
Dimension - B Outside Diameter inch	1.25 in
Dimension - Inside Diameter inch	0.98 in
Dimension - L Length Overall mm	129 mm
Dimension - Length Overall inch	5.06 in
Dimension - Outside Diameter inch	1.25 in
Dimension - P inch	1.18 in
Dimension - Strip Length inch	3.38 in
Equivalent Cross Pin Size	0.59 in. - 350 kcmil
Equivalent Pin Size	350 kcmil

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	535 DLO
Conductor - Copper DLO Size Range	535.3 (1325/#24) DLO
Conductor - Copper Flex G Size	550 kcmil
Conductor - Copper Flex H Size	550 kcmil
Conductor - Copper Flex I Size	550 kcmil
Conductor - Copper Str Size	550 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)