

YE38P67X134FX

by Burndy
Catalog ID: YE38P67X134FX

Prop 65 Notice

Cu Compression Adaptor Plugs, 535.5 kcmil(1325/#24)DLO (500 kcmil Nom.), 5.22" L



Product Details

General

Color Code	Pink
Connector Type	Pin Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810038284
UPC 12 Digit	7818100382844

Dimensions

Dimension - A Outside Diameter inch	0.67 in
Dimension - B Length fraction	3-5/16 in
Dimension - B Length inch	3.29 in
Dimension - B Outside Diameter inch	1.25 in
Dimension - Inside Diameter inch	0.98 in
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.22 in
Dimension - Outside Diameter inch	1.25 in
Dimension - P inch	1.34 in
Dimension - Strip Length inch	3.38 in
Equivalent Cross Pin Size	0.67 in. - 450 kcmil
Equivalent Pin Size	450 kcmil

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	535 DLO
Conductor - Copper DLO Size Range	535.3 (1325/#24) DLO
Conductor - Copper Flex G Size	550 kcmil
Conductor - Copper Flex H Size	550 kcmil
Conductor - Copper Flex I Size	550 kcmil
Conductor - Copper Str Size	550 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)