

# YE38P85X156

by Burndy  
Catalog ID: YE38P85X156

Cu Adaptor Plugs, 535.5 kcmil (1325/#24)DLO Cu



## Product Details

### General

Connector Type	Pin Terminal
Die Index	L99
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Copper Pin Adapters
UPC	781810038635
UPC 12 Digit	7818100386355

### Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.88 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.02 in
Dimension - Outside Diameter inch	1.25 in
Dimension - P inch	1.56 in
Dimension - Strip Length inch	1 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	535.3 (1325/#24)
Conductor - Copper DLO Size Range	535.3 (1325/#24)

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	20
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)