

YE39P71X142

by Burndy
Catalog ID: YE39P71X142

Prop 65 Notice

Cu Adaptor Plugs, 750 KCMIL (Code), 5.41 IN L, Compression, Black, 24 Index, 3-5/8 IN Strip Length



Product Details

General

Color Code	Black
Connector Type	Pin Terminal
Die Index	24
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810037164
UPC 12 Digit	7818100371644

Dimensions

Dimension - A Outside Diameter inch	0.71 in
Dimension - B Length fraction	3-3/8 in
Dimension - B Length inch	3.37 in
Dimension - B Outside Diameter inch	1.30 in
Dimension - Inside Diameter inch	1.03 in
Dimension - L Length Overall mm	137 mm
Dimension - Length Overall inch	5.41 in
Dimension - Outside Diameter inch	1.30 in
Dimension - P inch	1.42 in
Dimension - Strip Length inch	3.62 in
Equivalent Cross Pin Size	0.71 in. - 500 kcmil
Equivalent Pin Size	500 kcmil

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size Range	750
Conductor - Copper Flex H Size Range	750
Conductor - Copper Flex I Size Range	750
Conductor - Copper Flex K Size Range	750
Conductor - Copper Flex M Size Range	750
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)