

## YE39P87X174

by Burndy  
Catalog ID: YE39P87X174

Cu Adaptor Plugs, 750 KCMIL (Code), 5.73 IN L, Compression, Black, 24 Index, 3-5/8 IN Strip Length



### Product Details

#### General

Color Code	Black
Connector Type	Pin Terminal
Die Index	24
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810038116
UPC 12 Digit	7818100381166

#### Dimensions

Dimension - A Outside Diameter inch	0.87 in
Dimension - B Length fraction	3-3/8 in
Dimension - B Length inch	3.37 in
Dimension - B Outside Diameter inch	1.30 in
Dimension - Inside Diameter inch	1.03 in
Dimension - L Length Overall mm	146 mm
Dimension - Length Overall inch	5.73 in
Dimension - Outside Diameter inch	1.30 in
Dimension - P inch	1.74 in
Dimension - Strip Length inch	3.62 in
Equivalent Cross Pin Size	0.87 in. - 750 kcmil
Equivalent Pin Size	750 kcmil

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper Flex G Size Range	750
Conductor - Copper Flex H Size Range	750
Conductor - Copper Flex I Size Range	750
Conductor - Copper Flex K Size Range	750
Conductor - Copper Flex M Size Range	750
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)