

# YE44P71X142FX

by Burndy  
Catalog ID: YE44P71X142FX

Prop 65 Notice

Copper Adaptor Plugs, 777.7 (1925/#24) DLO, L115 Index, Wire Strip Length: 3-5/8 IN



## Product Details

### General

Color Code	Yellow
Connector Type	Pin Terminal
Die Index	L115
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYPLUG™
Type	Copper Pin Adapters
UPC	781810038246
UPC 12 Digit	7818100382466

### Dimensions

Dimension - B Length fraction	3-9/16 in
Dimension - B Length inch	3.54 in
Dimension - Inside Diameter inch	1.17 in
Dimension - L Length Overall mm	144 mm
Dimension - Length Overall inch	5.67 in
Dimension - Outside Diameter inch	1.50 in
Dimension - P inch	1.42 in
Equivalent Cross Pin Size	0.71 in. - 500 kcmil
Equivalent Pin Size	500 kcmil

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24) DLO
-----------------------------	----------------------

Conductor - Copper DLO Size Range	777.7 (1925/#24) DLO
-----------------------------------	----------------------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)