

# YE44P78X156FX

by Burndy  
Catalog ID: YE44P78X156FX

Prop 65 Notice

Copper Adaptor Plugs, 777.7 kcmil (1925/24) (750 kcmil Nom), L115 Index,  
Cable Strip Length: 3-5/8 IN



## Product Details

### General

Color Code	Yellow
Connector Type	Pin Terminal
Die Index	L115
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYPLUG™
Type	Copper Pin Adapters
UPC	781810038208
UPC 12 Digit	7818100382088

### Dimensions

Dimension - B Length fraction	3-9/16 in
Dimension - B Length inch	3.54 in
Dimension - Inside Diameter inch	1.17 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.81 in
Dimension - Outside Diameter inch	1.50 in
Dimension - P inch	1.56 in
Dimension - Strip Length inch	3-5/8
Equivalent Cross Pin Size	0.78 in. - 600 kcmil
Equivalent Pin Size	600 kcmil

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24) DLO
Conductor - Copper DLO Size Range	777.7 (1925/#24) DLO

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)