

YE44P87X174FX

by Burndy
Catalog ID: YE44P87X174FX

Cu Compression Adaptor Plugs, 777.7 kcmil (1925/#24)DLO (750 kcmil Flex)



Product Details

General

Color Code	Yellow
Connector Type	Pin Terminal
Die Index	L115
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYPLUG™
Type	Copper Pin Adapters
UPC	781810038161
UPC 12 Digit	7818100381611

Dimensions

Dimension - B Length fraction	3-9/16 in
Dimension - B Length inch	3.54 in
Dimension - Inside Diameter inch	1.17 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	5.99 in
Dimension - Outside Diameter inch	1.50 in
Dimension - P inch	1.74 in
Dimension - Strip Length inch	3-5/8
Equivalent Cross Pin Size	0.87 in. - 750 kcmil
Equivalent Pin Size	750 kcmil

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24) DLO
Conductor - Copper DLO Size Range	777.7 (1925/#24) DLO

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)