

YEVI1CP26X75FX

by Burndy
Catalog ID: YEVI1CP26X75FX

Prop 65 Notice

Copper Adaptor Plugs, #1 Str. (175/24-225/24) Flex, #1 AWG Code, 11 Index, Cable Strip Length: 1-3/4 IN



Product Details

General

Color Code	Green
Connector Type	Pin Terminal
Die Index	11
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYPLUG™
Type	Copper Pin Adapters
UPC	781810037843
UPC 12 Digit	7818100378433

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.66 in
Dimension - Inside Diameter inch	0.39 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.63 in
Dimension - Outside Diameter inch	0.51 in
Dimension - P inch	0.75 in
Dimension - Strip Length inch	1-3/4
Equivalent Cross Pin Size	0.26 in. - 2 AWG
Equivalent Pin Size	2 AWG

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1 (225/#24) DLO
Conductor - Copper DLO Size Range	1 (225/#24) DLO
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex G Size Range	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex H Size Range	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex I Size Range	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex K Size Range	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Copper Flex M Size Range	1 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)