

YEV25P29X75FX

by Burndy
Catalog ID: YEV25P29X75FX

Prop 65 Notice

Cu Adaptor Plugs, 1/0 STR (275/#24) DLO, 1/0 AWG Code, 100 Navy, 600V, Compression



Product Details

General

Color Code	Pink
Connector Type	Pin Terminal
Die Index	12
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYPLUG™
Type	Copper Pin Adapters
UPC	781810037850
UPC 12 Digit	7818100378500

Dimensions

Dimension - B Length fraction	1-13/16 in
Dimension - B Length inch	1.80 in
Dimension - Inside Diameter inch	0.44 in
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.80 in
Dimension - Outside Diameter inch	0.56 in
Dimension - P inch	0.75 in
Dimension - Strip Length inch	1-7/8
Equivalent Cross Pin Size	0.29 - 1 AWG
Equivalent Pin Size	1 AWG

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24) DLO
Conductor - Copper DLO Size Range	1/0 (275/#24) DLO
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Flex M Size Range	1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)