

YEV2CP23X75FX

by Burndy
Catalog ID: YEV2CP23X75FX

Prop 65 Notice

Cu Adaptor Plugs, #2 STR (125/#24-150/#24) DLO, #2 AWG Code, 60 Navy, Compression



Product Details

General

Color Code	Brown
Connector Type	Pin Terminal
Die Index	10
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYPLUG™
Type	Copper Pin Adapters
UPC	781810037836
UPC 12 Digit	7818100378366

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.65 in
Dimension - Inside Diameter inch	0.36 in
Dimension - L Length Overall mm	66 mm
Dimension - Length Overall inch	2.60 in
Dimension - Outside Diameter inch	0.46 in
Dimension - P inch	0.75 in
Dimension - Strip Length inch	1-3/4
Equivalent Cross Pin Size	0.23 in. - 3 AWG
Equivalent Pin Size	3 AWG

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	2 (150/#24) DLO
Conductor - Copper DLO Size Range	2 (150/#24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Flex M Size Range	2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)