

YF2210FL

by Burndy
Catalog ID: YF2210FL

Ratchet Ferrule Crimp Tool, Dieless, #22-#10 AWG, Weight-82 lbs.

- Front load crimping position
- Dieless crimping without multiple grooves
- Full cycle ratchet mechanism
- Ratchet release lever

Features: Ratchet Ferrule Crimp Tool, Dieless, Weight-82 lbs 5 year limited warranty



Product Details

General

| | |
|--------------|--------------------------------|
| Application | Crimping |
| Die Type | Dieless |
| Sub Brand | FERRULES |
| Tool Type | Ratchet Front Load Crimp Tools |
| Type | Crimpers |
| UPC | 781810542644 |
| UPC 12 Digit | 7818105426444 |

Dimensions

| | |
|--------|---------|
| Height | 1.00 in |
| Length | 7.75 in |
| Weight | 0.82 lb |
| Width | 2.32 in |

Conductor Related

| | |
|-------------------------------------|---------------------------|
| Conductor - Copper Solid Size Range | 22 -10 AWG |
| Conductor - Copper Str Size Range | 20 AWG-10 AWG |
| Crimping Ranges | Copper: #22 AWG - #10 AWG |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)