

# YF2807UI

by Burndy  
Catalog ID: YF2807UI

Prop 65 Notice

Cu Alloy Bare Ferrule, Smooth Funnel Entry, 28 AWG, 0.28" L, Seamless bbl, Tin Plated, For Use On Cu Cond



## Product Details

### General

Material	Copper
Type	Bootlace Ferrule
UPC	781810479254
UPC 12 Digit	7818104792544

### Dimensions

Dimension - D inch	0.04 in
Dimension - D1 inch	0.03 in
Dimension - D2 inch	0.08 in
Dimension - Length Side A inch	0.28 in
Length	0.276 in
Width	0.079 in

### Conductor Related

Conductor - Copper Solid Size	28 AWG
Conductor - Copper Str Size	28 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	1000

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)