

YFMR28

by Burndy
Catalog ID: YFMR28

Prop 65 Notice

For Use with MOLIMITER™ Assembly.



Product Details

General

Connector Type	Limiter
Plated	Y
Plating Type	Tin - Hot Dipped
Trade Name	MOLIMITER™
UPC	781810262337
UPC 12 Digit	7818102623377

Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.86 in
Dimension - Inside Diameter inch	0.55 in
Dimension - Length Overall inch	6.28 in
Dimension - Outside Diameter inch	0.83 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)