

YFO140

by Burndy
Catalog ID: YFO140

H-Tap connector, 1/0-6 str(Run) 1-6 str(Tap)(Al or Cu),2/0-6(Run) 1-6 str(Tap)(Compact), 600V-35KV, Tin plated, Green , O index



Product Details

General

Color Code	Green
Connector Type	H-Tap
Die Index	O
Material	Aluminum
Plated	NO
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
Type	Compression Taps
UPC	781810737989
UPC 12 Digit	7818107379899

Dimensions

Dimension - Height inch	1.15 in
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.62 in
Dimension - Strip Length inch	1-7/8
Dimension - Width inch	0.70 in
Dimension - Width mm	18 mm

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Run	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Run Range	6 AWG-1/0 AWG
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - AL Str Tap Range	6 AWG-1 AWG
Conductor - Copper Str Compact Run	6 AWG;4 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Str Compact Run Range	6 AWG-2/0 AWG

Conductor - Copper Str Compact Tap	6 AWG;4 AWG;2 AWG;1 AWG
Conductor - Copper Str Compact Tap Range	6 AWG-1 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Run Range	6 AWG-1/0
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Tap Range	6 AWG-1 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)