

YFR865

by Burndy
Catalog ID: YFR865

Uninsulated Aluminum Compression Tap Connectorul Listed 90°C, 600 Volts To 35 Kv.



Product Details

General

Color Code	Yellow
Connector Type	H-Tap
Die Index	KR
Material	Aluminum
Plated	NO
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
Type	Compression Taps
UPC	781810738221
UPC 12 Digit	7818107382211

Dimensions

Dimension - Height inch	3.04 in
Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.62 in
Dimension - Strip Length inch	5
Dimension - Width inch	1.74 in
Dimension - Width mm	44 mm

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil
Conductor - AL Str Run Range	600 kcmil-900 kcmil
Conductor - AL Str Tap	350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Tap Range	350 kcmil-600 kcmil
Conductor - Copper Str Compact Run	700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil

Conductor - Copper Str Compact Run Range	700 kcmil-900 kcmil
Conductor - Copper Str Compact Tap	400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Compact Tap Range	400 kcmil-600 kcmil
Conductor - Copper Str Run	600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil
Conductor - Copper Str Run Range	600 kcmil-900 kcmil
Conductor - Copper Str Tap	350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Tap Range	350 kcmil-600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)