

# YFR965

by Burndy  
Catalog ID: YFR965

Uninsulated Aluminum Compression Tap Connectorul Listed 90°C, 600 Volts To 35 Kv.



## Product Details

### General

Color Code	Yellow
Connector Type	H-Tap
Die Index	KR
Material	Aluminum
Plated	NO
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
Type	Compression Taps
UPC	781810100110
UPC 12 Digit	7818101001100

### Dimensions

Dimension - Height inch	3.15 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Dimension - Strip Length inch	6-1/4
Dimension - Width inch	1.67 in
Dimension - Width mm	42 mm

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - AL Str Run	350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Run Range	350 kcmil-1000 kcmil
Conductor - AL Str Tap	350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil

Conductor - AL Str Tap Range	350 kcmil-1000 kcmil
Conductor - Copper Str Compact Run	400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;650 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Compact Run Range	400 kcmil-1000 kcmil
Conductor - Copper Str Compact Tap	400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;650 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Compact Tap Range	400 kcmil-1000 kcmil
Conductor - Copper Str Run	350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	350 kcmil-1000 kcmil
Conductor - Copper Str Tap	350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	350 kcmil-1000 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)