



YFTW0814W

by Burndy
Catalog ID: YFTW0814W

Prop 65 Notice

Elect Cu Twin Insul Wire Ferrules, Smooth Funnel Entry, 8 AWG, 1.04" L, Tin Plated, Beige, For use on Cu Cond.

Features: Made Of Electrolytic Copper, Tin Plated, Smooth Funnel Entry To Make Wire Insertion Easier, Secure Contacting Even After Multiple Reconnections, Long-Term Contact Resistance, No Fraying Of Strands, No Breakage Of Wire Strands When Wire Is Bent, Under Stress Or In Vibration Environment, Tooling: YF2210TOOL

Product Details

General

Application	For Use On Copper Conductor Used To Terminate Stranded Wires
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	BARE FERRULES
Type	Bootlace Ferrule
UPC	781810482124
UPC 12 Digit	7818104821244

Dimensions

Dimension - D inch	0.27 in
Dimension - D1 inch	0.25 in
Dimension - D2 inch	0.51 in
Dimension - Length Side A inch	1.04 in
Dimension - Length Side B inch	0.55 in

Conductor Related

Conductor - Copper Solid Size	8 AWG
Conductor - Copper Str Size	8 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)