



YGA282N90

by Burndy
Catalog ID: YGA282N90

Grounding Irreversible Compression Terminals.

Product Details

General

Color Code	Purple
Connector Type	Terminal
Die Index	15
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810267158
UPC 12 Digit	7818102671588

Dimensions

Dimension - B Length fraction	1-3/5 in
Dimension - B Length inch	1.59 in
Dimension - Height fraction	2-2/5 in
Dimension - Height inch	2.39 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	131 mm
Dimension - Length Overall inch	5.17 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-11/16
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)