

YGA8CTC14

by Burndy
Catalog ID: YGA8CTC14

Prop 65 Notice

Grounding Irreversible Compression Terminals.



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810102442
UPC 12 Digit	7818101024422

Dimensions

Dimension - B Length fraction	4/5 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size inch	0.25 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	8
Conductor - Copper Solid Size Range	8
Conductor - Copper Str Size	8 Sol./8 Str.

Conductor - Copper Str Size Range	8 Sol./8 Str.
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)