

YGC6C8

by Burndy
Catalog ID: YGC6C8

Prop 65 Notice

Copper Compression C Tap, 6 AWG(Run)/8 AWG(Tap)



Product Details

General

| | |
|--|---------------|
| Connector Type | Tap |
| Die Index | BG |
| Material | Copper |
| Physical Attribute - Number of Crimps Required | 2 |
| Plated | N |
| Plating Type | Unplated |
| Trade Name | CRIMPIT™ |
| Type | Taps |
| UPC | 781810102596 |
| UPC 12 Digit | 7818101025966 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Height fraction | 46/63 in |
| Dimension - Height inch | 0.73 in |
| Dimension - L Length Overall mm | 16 mm |
| Dimension - Length Overall inch | 0.62 in |

Conductor Related

| | |
|------------------------------------|-------|
| Conductor - Copper Solid Run | 6 AWG |
| Conductor - Copper Solid Run Range | 6 AWG |
| Conductor - Copper Solid Tap | 8 AWG |
| Conductor - Copper Solid Tap Range | 8 AWG |
| Conductor - Copper Str Run | 6 AWG |
| Conductor - Copper Str Run Range | 6 AWG |
| Conductor - Copper Str Tap | 8 AWG |
| Conductor - Copper Str Tap Range | 8 AWG |

Certifications and Compliance

| | |
|---|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |

| | |
|------------------------------------|-------|
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)