

# YGC8C8

by Burndy  
Catalog ID: YGC8C8

Prop 65 Notice

Copper Crimpit, .52 in L, #8 Sol. #8 Str. (Run) , #8 Sol. #8 Str. (Tap).

Features: UL467 Listed For Direct Burial In Earth Or Concrete, Prefilled With PENETROX E2 Oxide Inhibitor, Die Index: 162 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W162 Die, (2), OUR840 Tool, W162 Die, (2)



## Product Details

### General

Application	For Direct Burial In Earth Or Concrete
Connector Type	Tap
Die Index	162
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, CRIMPIT
Trade Name	CRIMPIT™
Type	Taps
UPC	781810102558
UPC 12 Digit	7818101025588

### Dimensions

Dimension - Height fraction	23/50 in
Dimension - Height inch	0.46 in
Dimension - L Length Overall mm	13 mm
Dimension - Length Overall inch	0.52 in

### Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	8 AWG
Conductor - Copper Str Run	8 AWG
Conductor - Copper Str Run Range	8 AWG
Conductor - Copper Str Tap	8 AWG
Conductor - Copper Str Tap Range	8 AWG

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)