

## YGF294N75

by Burndy  
Catalog ID: YGF294N75

Copper Compression Grounding Plate, 4 Hole w/o Inspection Hole, 2-250 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 3/4-10, 0.81 EFF Thread.



## Product Details

### General

Die Index	997
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Tapped Holes	4
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
UPC	781810144411
UPC 12 Digit	7818101444111

### Dimensions

Dimension - D inch	3.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	3-31/50 in
Dimension - Height inch	3.62 in
Dimension - L Length Overall mm	147 mm
Dimension - Length Overall inch	5.78 in
Dimension - Pad Width inch	3.25 in
Dimension - Thread Size	3/4-10, 0.81 EFF Thread
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2 AWG-250 kcmil
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	NEMA Size Holes
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL467</li><li>• IEEE 837</li></ul>
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)