



YGF344N50

by Burndy
Catalog ID: YGF344N50

Prop 65 Notice

Copper Compression Grounding Plate, 4 Hole, 250- 500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 1/2-13, .94 EFF Thread.

Product Details

General

Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Tapped Holes	4
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
UPC	781810220559
UPC 12 Digit	7818102205599

Dimensions

Dimension - D inch	3.75 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	4-31/50 in
Dimension - Height inch	4.62 in
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.90 in
Dimension - Pad Width inch	3.75 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	NEMA Size Holes
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• IEEE 837
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)