

YGHA28NTN

by Burndy
Catalog ID: YGHA28NTN

Prop 65 Notice

Tin Plated Heavy Duty Irreversible Compression Terminals



Product Details

General

Connector Type	Terminal
Die Index	17
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Terminals
UPC	781810234860
UPC 12 Digit	7818102348600

Dimensions

Dimension - B Length fraction	1-9/50 in
Dimension - B Length inch	1.18 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.18 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Pad Width inch	1.22 in
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL468A-468B • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)