

YGHA2CNTN

by Burndy
Catalog ID: YGHA2CNTN

Prop 65 Notice

Tin Plated Heavy Duty Irreversible Compression Terminals



Product Details

General

Connector Type	Terminal
Die Index - Element B	11
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Terminals
UPC	621945454743
UPC 12 Digit	6219454547433

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	2.46 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.50 in
Dimension - Pad Width inch	0.97 in
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	Yes

Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• UL468A-468B• IEEE 837
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)