

# YGHA362N

by Burndy  
Catalog ID: YGHA362N

Prop 65 Notice

Heavy Duty Irreversible Compression Terminals.



## Product Details

### General

Connector Type	Terminal
Die Index	576
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810340356
UPC 12 Digit	7818103403566

### Dimensions

Dimension - B Length fraction	1-19/50 in
Dimension - B Length inch	1.38 in
Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	139 mm
Dimension - Length Overall inch	5.48 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.55 in
Dimension - Pad Width inch	2.10 in
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	IEEE 837
Standards - Industry Standards Met	IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)