

YGHC26C26TN

by Burndy
Catalog ID: YGHC26C26TN

Prop 65 Notice

Cu Compression Ground Tap Connector, 1 str to 2/0 str, 3/8 " Rod (Run), 1 str to 2/0 str (Tap), Tin Plated



Product Details

General

Connector Type	Tap
Die Index	O
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810171608
UPC 12 Digit	7818101716088

Dimensions

Dimension - Height fraction	1-27/50 in
Dimension - Height inch	1.54 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in

Conductor Related

Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	1 AWG-2/0 AWG
Conductor - Copper Str Tap	1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	1-2/0
Conductor - Rod Run	3/8 in
Conductor - Rod Run Range	3/8 in

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial

Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• IEEE 837• UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)