



YGHC29C29NP

by Burndy
Catalog ID: YGHC29C29NP

Prop 65 Notice

Copper Compression Ground Connector; 3/0 Str.-250 kcmil (Run & Tap); 997 Index, NO Penetrox™

Product Details

General

Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYTAP™
Type	Taps
UPC	781810568903
UPC 12 Digit	7818105689033

Dimensions

Dimension - L Length Overall mm	997 mm
---------------------------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> UL Listed to UL 467 CSA Certified to C22.2 No.41
Standards - Industry Standards Met	<ul style="list-style-type: none"> UL467 IEEE 837 UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)