



YGHC29C29TN

by Burndy
Catalog ID: YGHC29C29TN

Prop 65 Notice

Copper Compression C Connector, 3/0 AWG(Str) - 250 kcmil, 1/2" or 5/8" Rod (Run) & 3/0 AWG(Str) - 250 kcmil (Tap), Tin Plated

Product Details

General

Connector Type	Tap
Die Index	997
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYGROUND®
Type	Taps
UPC	781810085288
UPC 12 Digit	7818100852888

Dimensions

Dimension - Height fraction	2-3/50 in
Dimension - Height inch	2.06 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Run	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	3/0 AWG-250 kcmil
Conductor - Copper Str Tap	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	3/0-250
Conductor - Rod Run	1/2 in;5/8 in
Conductor - Rod Run Range	1/2 in-5/8 in

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837 • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)