

YGHC2C2MX

by Burndy
Catalog ID: YGHC2C2MX

Prop 65 Notice

Comp Ground Tap Connector, #6 Sol- #2 Str(Groove A), #6 Sol-#2 Str(Groove B), No Stamping,PENETROX or VAC Form Packaging, Bulk Shipped



Product Details

General

Connector Type	Tap
Die Index	C
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Type	Taps
UPC	781810308691
UPC 12 Digit	7818103086911

Dimensions

Dimension - Height fraction	1-4/25 in
Dimension - Height inch	1.16 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in

Conductor Related

Conductor - Copper Solid Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Run Range	6 AWG-1 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Tap Range	6 AWG-1 AWG
Conductor - Copper Str Run	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	7 AWG-2 AWG
Conductor - Copper Str Tap	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	7-2
Conductor - Rod Run	1/4 in
Conductor - Rod Run Range	1/4 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837 • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)