

YGHC34C26TN

by Burndy
Catalog ID: YGHC34C26TN

Prop 65 Notice

Cu Compression Ground Tap Connector, .88 IN L, 300-500 Kcmil (Run), #6 Sol. To 2/0 str (Tap), Tin Plated



Product Details

General

Connector Type	Tap
Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810327937
UPC 12 Digit	7818103279377

Dimensions

Dimension - Height fraction	2-21/50 in
Dimension - Height inch	2.42 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-3/0 AWG
Conductor - Copper Str Run	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Tap	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	7 AWG-2/0 AWG
Conductor - Rod Run	3/4 in
Conductor - Rod Run Range	3/4 in

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)