



## YGHC34C34TN

by Burndy  
Catalog ID: YGHC34C34TN

Prop 65 Notice

Cu Compression Ground Tap Connector, 1.10 IN L, 300-500 Kcmil (Run), 300-500 Kcmil (Tap)), Tin Plated

## Product Details

### General

Connector Type	Tap
Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810110874
UPC 12 Digit	7818101108744

### Dimensions

Dimension - Height fraction	2-81/89 in
Dimension - Height inch	2.91 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.10 in

### Conductor Related

Conductor - Copper Str Run	300;350;400;450;500
Conductor - Copper Str Run Range	300-500
Conductor - Copper Str Tap	300;350;400;450;500
Conductor - Copper Str Tap Range	300-500

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>UL467</li> <li>IEEE 837</li> <li>UL468A-468B</li> </ul>

Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)