

YGHHA31NTN

by Burndy
Catalog ID: YGHHA31NTN

Prop 65 Notice

Ground Connector; 350 kcmil; 1/2"; 1.62 in L; 4.09 in W



Product Details

General

Connector Type	Terminal
Die Index	20
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Type	Terminals
UPC	781810444832
UPC 12 Digit	7818104448322

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.09 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.17 in
Dimension - Pad Width inch	1.62 in
Dimension - Width fraction	16/39 in
Dimension - Width inch	0.41 in
Dimension - Z inch	0.66 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)