


YGHHC26C26

by Burndy
Catalog ID: YGHHC26C26

Prop 65 Notice

Hytap Connector, Compression Ground, Cable Range: 1 STR - 2/0 STR (RUN), 1 STR - 2/0 STR (TAP), Height: 1.54 in, Length: 0.75 in, Z: 1.88 in

Irreversible compression ground tap figure C connector. Accomadates all cable combinations from #6 solid through 500 kcmil



Product Details

General

Application	Cable to Cable or Cable to Ground Rod Applications
Connector Type	Tap
Construction Material - Main	Copper
Die Index	O
Material	Copper
Plated	N
Sub Brand	Connector
Trade Name	HYTAP™
Type	Taps
UPC	621945456228
UPC 12 Digit	6219454562288

Dimensions

Dimension - Height inch	1.54
Dimension - Width inch	1.88
Height	1.54 in
Width	1.88 in

Conductor Related

Conductor - Copper Str Run Range	1 Stranded - 2/0 Stranded
Conductor - Copper Str Tap Range	1 Stranded - 2/0 Stranded
Conductor - Rod Run Range	3/8" Rod
Conductor - Rod Size Range	3/8" Rod
Conductor - Rod Tap Range	3/8" Rod

Certifications and Compliance

Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none"> • UL 467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)