


## YGHHC29C26

by Burndy  
Catalog ID: YGHHC29C26

Prop 65 Notice

Compression ground connector, Material: Copper, Range Run: 3/0 Str-250 Kcmil, Tap: #6 sol-2/0 Str.

Ground connector, Material: Copper, Range Run: 3/0 Str-250 Kcmil, Tap: #6 Sol-2/0 Str, H:1.97, Number of crimps: 2



## Product Details

### General

Application	For Direct Burial cables
Connector Type	Tap
Die Index	997
Material	Copper
Plated	N
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	621945456235
UPC 12 Digit	6219454562355

### Conductor Related

Conductor - Copper Solid Tap Range	6 Solid - 2/0 Solid
Conductor - Copper Str Run Range	3/0 Stranded - 250 kcmil
Conductor - Copper Str Tap Range	6 Stranded - 2/0 Stranded
Conductor - Rod Run Range	1/2" or 5/8" Rod

### Certifications and Compliance

Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL 467</li> <li>• IEEE 837</li> <li>• IEEE 837 2014 Qualified</li> <li>• UL 486A-486B</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> <li>• IEEE 837 2014 Qualified</li> <li>• UL 486A-486B</li> </ul>

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

1
---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)