


YGHHC29C29

by Burndy
Catalog ID: YGHHC29C29

Prop 65 Notice

Compression ground connector, Material: Copper, Range Run: 3/0 Str-250 Kcmil, Tap: 3/0 Str-250 Kcmil.

Ground connector, Material: Copper, Range Run: 3/0 Str-250 Kcmil, Tap: #6 sol-2/0 Str, H:2.06, Number of crimps: 2



Product Details

General

Application	For Direct Burial cables
Connector Type	Tap
Die Index	997
Material	Copper
Plated	N
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	621945456242
UPC 12 Digit	6219454562422

Conductor Related

Conductor - Copper Str Run Range	3/0 Stranded - 250 kcmil
Conductor - Copper Str Tap Range	3/0 Stranded - 250 kcmil
Conductor - Rod Run Range	1/2"; 5/8"

Certifications and Compliance

Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none"> • UL 467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)